

5.0×3.2mm for Consumer Products



RoHS Compliant

Features

- Crystal unit for Consumer Products
- Small and low profile (5.0×3.2×1.3mm)
- Ceramic package
- Reflow compatible

Applications

- Digital Electronics
- Consumer Products

How to Order

CX5032GA 08000 H0 H E Q Z1
 ① ② ③ ④ ⑤ ⑥ ⑦

- ① Series
- ② Frequency
- ③ Load Capacitance
- ④ Frequency Tolerance
- ⑤ Operating Temp. Range
- ⑥ Frequency Temp. Stability
- ⑦ Individual Specification (STD Standard is "Z1")

H0	12 pF	Q	±20×10 ⁻⁶
EQ	-10 to +70°C		±30×10 ⁻⁶

Packaging (Tape & Reel 1000 pcs./ reel)

Specifications

Item	Symbol	Specification	Units	Remarks
Frequency Range	f _{nom}	8000 to 40000	kHz	
Overtone Order	OT	Fundamental	—	
Load Capacitance	CL	12	pF	Please contact us for other Load Capacitance.
Frequency Tolerance	f _{tol}	±20	×10 ⁻⁶	25°C±3°C
Motional Series Resistance	R1	Table 1	ohm	
Drive Level	DL	Table 2	μW	
Operating Temp. Range	T _{use}	-10 to +70	°C	
Storage Temp. Range	T _{stg}	-40 to +85	°C	
Frequency Temp. Characteristics	f _{tem}	±30	×10 ⁻⁶	Freq. deviation from the value at 25°C

Please contact us for other specifications.

Table1 Motional Series Resistance


Frequency Range	Motional Series Resistance
8000 ≤ f _{nom} < 9500kHz	300Ω max.
9500 ≤ f _{nom} < 10000kHz	200Ω max.
10000 ≤ f _{nom} < 14000kHz	150Ω max.
14000 ≤ f _{nom} < 20000kHz	100Ω max.
20000 ≤ f _{nom} < 30000kHz	70Ω max.
30000 ≤ f _{nom} ≤ 40000kHz	50Ω max.

Table2 Level of Drive

Frequency Range	Level of Drive
8000 ≤ f _{nom} < 16000kHz	10μW (500μW max.)
16000 ≤ f _{nom} < 25000kHz	10μW (300μW max.)
25000 ≤ f _{nom} ≤ 40000kHz	10μW (100μW max.)

Dimensions

(Unit: mm)



Recommended Land Pattern

(Unit: mm)

